


FASTCAM SA2

HIGH-DEFINITION HIGH-SPEED VIDEO SYSTEM



2,048 x 2,048 (4MEGA pixel) resolution, developed for a broad range of applications including automotive safety testing, defense, fluid dynamics and materials research

The FASTCAM SA2 has been engineered to provide the optimum speed and resolution required for detailed observation and analysis of high speed events occurring in large spatial areas or fields of view. The 10 μm pixels lend themselves perfectly to micro analysis applications such as Particle Image Velocimetry (PIV) or Digital Image Correlation (DIC).

Areas where a high degree of motion analysis precision is demanded, such as automotive safety testing, weapons performance testing, fluid dynamics and solid mechanics will benefit from the combination of very high resolution, high framing rates, and typical Photron reliability.

The ability to operate at full HD resolution (1920 x 1080 pixels) at up to 2,000 fps will be a huge benefit to broadcast applications, including sports, nature documentaries, advertising and motion picture entertainment. The FASTCAM SA2 builds on Photron's Emmy award winning experience and is backed by the industry's best reputation for reliability and support.

As with every Photron high speed camera, ease of use and attention to details make the difference, with the FASTCAM SA2 supplied with the very easy to use Photron FASTCAM Viewer (PFV) software, or for those applications where a computer is not an option, an RS-422 optional keypad for camera control and image review.

Benefits

- Performance examples:
 - 2,048 x 2,048 pixels @ 1,080 fps
 - 1,920 x 1,080 pixels @ 2,000 fps
 - 1,024 x 1,024 pixels @ 3,200 fps
- Full HD resolution (1,920 x 1080 pixels) to 2,000 fps
- Incorporates Peltier temperature stabilized sensor and on-chip microlens array for optimum image quality and light sensitivity
- Available with three memory configurations:
 - 8GB for 1.29 seconds at 2,000 fps @ 1,920 x 1080 pixels
 - 16GB for 2.58 seconds at 2,000 fps @ 1,920 x 1080 pixels
 - 32GB for 5.17 seconds at 2,000 fps @ 1,920 x 1080 pixels
- Rear panel has dual HD-SDI and one RS-170 BNC outputs for real time monitoring during setup, recording and playback
- Photron FASTCAM Viewer (PFV) computer control via the Gigabit Ethernet port
- Four user selectable function buttons for easy rear panel control of camera
- Low-light mode for initial set up of camera position and focus
- Monochrome or color sensor captures 12-bit (36-bit color) uncompressed data




Photron

www.photron.com

FASTCAM SA2

HIGH-DEFINITION HIGH-SPEED VIDEO SYSTEM



Specifications: Partial Frame Rate / Recording Duration Table

FRAME RATE (fps)	MAXIMUM RESOLUTION Horizontal Vertical		MAXIMUM SHUTTER SPEED	RECORD DURATION (12-BIT)					
				TIME (Sec.)			FRAMES		
				8GB Model	16GB Model	32GB Model	8GB Model	16GB Model	32GB Model
1,000	2,048	2,048	2.76 μ s 1/367,000 sec	1.36	2.73	5.46	1,361	2,726	5,457
1,080	2,048	2,048		1.26	2.52	5.05	1,361	2,726	5,457
1,500	2,048	1,472		1.26	2.53	5.06	1,894	2,793	7,592
2,000	2,048	1,080		1.29	2.59	5.17	2,581	5,170	10,348
2,500	1,536	1,024		1.45	2.91	5.82	3,630	7,271	14,552
3,000	1,024	1,024		1.82	3.64	7.28	5,445	10,906	21,829
3,200	1,024	1,024		1.70	3.41	6.82	5,445	10,906	21,829
4,000	1,024	768		1.82	3.64	7.28	7,260	14,542	29,105
5,000	1,024	640		1.74	3.49	6.99	8,712	17,450	34,926
6,250	1,024	512		1.74	3.49	6.99	10,890	21,813	43,658
7,200	768	512		2.02	4.04	8.08	14,520	29,084	58,211
8,000	512	512		2.72	5.45	10.91	21,781	43,626	87,317
10,000	512	416		2.68	5.37	10.75	26,807	53,694	107,467
16,000	512	256		2.72	5.45	10.91	43,562	87,253	174,634
18,000	256	256		4.84	9.69	19.40	87,125	174,506	349,269
20,000	256	224		4.98	9.97	19.96	99,571	199,436	399,164
30,000	256	128		5.81	11.63	23.28	174,250	349,013	698,538
43,200	256	96		5.38	10.77	21.56	232,334	465,351	931,384
54,000	256	64		6.45	12.93	25.87	348,501	698,026	1,397,077
86,400	256	32		8.07	16.16	32.34	697,002	1,396,053	2,794,154

Sensor	10 μ m pixels, temperature stabilized, 12-bit ADC (Bayer system color, single sensor) with microlenses
Shutter	Global electronic shutter from 16.7ms to 2.76 μ s independent of frame rate
Lens Mount	Interchangeable F-mount and C-mount using supplied adapters, optional PL and B4 lens mounts
Extended Dynamic Range	Selectable in twenty steps (0 to 95% in 5% increments) to prevent pixel over-exposure
Memory	8GB (standard: 1,361 frames @ Maximum resolution) 16GB (option: 2,726 frames @ Maximum resolution) 32GB (option: 5,457 frames @ Maximum resolution)
Video Outputs	Live and playback video thorough Dual HD-SDI or single RS-170 (NTSC/PAL) outputs. Ability to zoom, pan and tilt within image via keypad.
Camera Control	Through optional keypad with integrated viewfinder and Gigabit Ethernet or RS-422
User Preset Switches	Four user selectable camera function controls mounted on the camera's rear panel
Low Light Mode	Low light mode drops the frame rate and shutter time to their maximum values, while maintaining other set parameters, to enable users to position and focus the camera
Triggering	Selectable positive or negative TTL 5Vp-p or switch closure
Trigger Delay	Programmable delay on selected input and output triggers, 100ns resolution
Timing	Internal clock or external source
Phase Lock	Enables cameras to be synchronized precisely together to a master camera or external source

Event Markers	Ten user entered event markers mark specific events within the image sequence in real time. Immediately accessible through software
Dual Speed Recording	Enables the recording speed to be changed up or down by a factor of 2, 4 or 8 during a recording
Trigger Modes	Start, End, Center, Manual, Random, Random Reset, Random Center, Random Manual and Duals Speed Recording
Saved Image Formats	JPEG, AVI, TIFF, BMP, RAW, PNG, MOV and FTIF. Images can be saved with or without image or comment data
Data Display	Frame Rate, Shutter Speed, Trigger Mode, Date or Time, Status (Playback/Record), Real Time, Frame Count and Resolution
Partitioning	Up to 64 memory segments for multiple recording in memory
Data Acquisition	Supports Photron MCDL and DAQ
Cooling	Actively cooled
Operating Temperature	0-40 degrees C (32 - 104 degree F)
Mounting	1 x 1/4 - 20 UNC, 1 x 3/8 - 16 UNC, 6x M6
Dimensions	165mm (6.5")H \times 153mm (6.02")W \times 250mm (9.84")D
Weight	6.9 kg (15.21 lbs)
Power Requirements	100V-240V AC \sim 1.5A, 50-60Hz DC operation 18-36 V DC, 100VA

Specifications subject to change without notice

PHOTRON USA, INC.
9520 Padgett Street, Suite 110
San Diego, CA 92126-4446
USA
Tel: 858.684.3555 or 800.585.2129
Fax: 858.684.3558
Email: image@photron.com
www.photron.com

PHOTRON (EUROPE) LIMITED
The Barn, Bottom Road
West Wycombe, Bucks, HP14 4BS
United Kingdom
Tel: +44 (0) 1494 481011
Fax: +44 (0) 1494 487011
Email: image@photron.com
www.photron.com

PHOTRON LIMITED
Fujimi 1-1-8
Chiyoda-Ku, Tokyo 102-0071
Japan
Tel: +81 (0) 3 3238 2107
Fax: +81 (0) 3 3238 2109
Email: image@photron.co.jp
www.photron.co.jp

Photron

SLOW MOTION IMAGING SOLUTIONS